


Dromex



NITRIFLEX PC GLOVE

EN 388:2003



4121



NITRIFLEX PC

Description

Dromex® Nitriflex PC, palm coated ultra-thin nitrile micro foam finish gloves, provide hands with excellent grip performance in wet, oil and dry environments. Sanitisation suppresses the reproduction of microbes, such as bacteria and fungi and hinders both unpleasant odours as well as material damage from mildew.

The nylon liner with spandex provides superior sensitivity and dexterity whilst the nitrile coating protects the hand from high abrasion and cut resistance with stronger tear resistant properties.

Suitable for applications of handling/assembling small oily parts, general assembly machining, micro-engineering and automotive components.

Special Instructions

Although the manufacturer has examined these gloves under the system for ensuring quality of production by means of monitoring and inspection, we recommend that all gloves should be thoroughly inspected before use to ensure no damage is present.

None of the materials or processes used in the manufacture of these products are known to be harmful to the wearer. The gloves and information contained herein are designed to accommodate the basic safety requirements and standards for Personal Protective Equipment. Actual conditions of use cannot be directly simulated in a test environment, therefore it is the responsibility of the user and not the manufacturer or supplier to determine the suitability for intended use.

Compliance & Conformity

Complies with the requirements of CE type examinations EN 420 for innocuousness, EN 388 for compliance with directive 89/686/EEC Mechanical Risks (4,1,2,1). Quality System conforms to ISO 9001:2008.

Specifications

Style: Palm and finger coated nitrile micro foam gloves
 Liner: Grey nylon spandex
 Palm: Black micro foam 0,04 mm ± 5%
 Back: 0,02 mm ± 5%
 Cuff: Nylon spandex composite knitted wrist
 Mass: 65± g per pair (size 11)

Sizes Available

8-11

Packaging, Storage & Obsolescence


Packed in individual polybags and sold as 120 pairs per carton for shipping. Store in a cool, dry, dark place. Stored correctly, the gloves physical properties will not change for up to 3 years.



Cleaning & Maintenance

Gloves should not be left in a contaminated condition if re-use is intended especially if potential hazards exist. Before removal from the hands excess contaminant should first be removed from the glove. Should this not be possible, it is advisable to ease left and right hand gloves off using the gloved hand and remove the gloves without the contaminant contacting the bare hands.

The gloves may then be decontaminated as indicated below.



Dromex® Nitriflex gloves have proven that dry cleaning as well as laundering are suitable cleaning methods.

We recommend that no bleaching or oxidising ingredients or any fabric softeners be used.

Recommended washing temperature is up to 40°C with mild detergents. The drying process may cause felting on the fabric surface. Drying temperature should not exceed 70°C (158°F).

There is no remarkable impact on cut resistance during the normal life cycle of a glove. Depending on glove construction, staining and cleaning method, the differences in shrinkage, yarn strength and colour may occur. In order to maximise the glove life cycle, we recommend the mildest possible cleaning conditions in terms of temperature, chemicals and cycle duration.

Due to a wide variety of possible constructions and combinations with other materials we recommend to always consult your professional cleaning service to determine the best suitable cleaning method.

Disposal

All industrial waste should be disposed of correctly according to local regulations and good disposal practice. Gloves should be disposed of considering the hazardous substances they were used for. Please consider recycling.

Materials



1. Wing thumb
2. Nitrile coated palm & fingers
3. Knit wrist

Marking



Dromex: Unit 1, 1 Blase Road, New Germany, 3620, South Africa
 T. +27(31) 713 1960 E. info@dromex.co.za
 www.dromex.co.za